

PRODUCT SPECIFICATION SHEET

Product Name: HellermannTyton® Thermal Transfer Ribbon

Part #	Description	Dimensions	Material, Color, Qty.	UV Resistant	Operating Temp.	Reach Compliant
HT-556-00165	Thermal Transfer Ribbon, SwiftMark	2.0" x 984', 1" Core	100 Resin, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-556-00205	Thermal Transfer Ribbon	2.24" x 154', 0.50" Core	822 Resin, White, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-556-00206	Thermal Transfer Ribbon	2.24" x 242', 0.5" Core	822 Resin, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-556-00190	Thermal Transfer Ribbon	4.33" x 229', 0.50" Core	PET, White, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM2	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Red, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM3	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Orange, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM4	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Yellow, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM5	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Green, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM6	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Blue, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM7	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Violet, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM8	Thermal Transfer Ribbon	4.33" x 242', 0.5" Core	PET, Silver, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TTDTHOUTSM	Thermal Transfer Ribbon	4.33" x 295', 0.50" Core	DTH Resin, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT10SM	Thermal Transfer Ribbon	4.33" x 299', 0.5" Core	822 Resin, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	No
HT-556-00189	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, White, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT2	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Red, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT3	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Orange, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT4	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Yellow, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT5	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Green, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT6	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Blue, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT7	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Purple, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes

Part #	Description	Dimensions	Material, Color, Qty.	UV Resistant	Operating Temp.	Reach Compliant
HT-TT822OUT8	Thermal Transfer Ribbon	4.33" x 984', 1" Core	PET, Silver, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT900OUT	Thermal Transfer Ribbon	4.0" x 985', 1" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TTDTHOUT	Thermal Transfer Ribbon	4.0" x 984', 1" Core	DTH Resin, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TTHSTOUT	Clean Start® Thermal Transfer Ribbon	4.0" x 984', 1.0" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT100OUTSM	Clean Start® Thermal Transfer Ribbon, Soft Resin	4.33" x 242', 0.5" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUTSM	Clean Start® Thermal Transfer Ribbon, Hard Resin	4.33" x 242', 0.5" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TTHSTOUTSM	Clean Start® Thermal Transfer Ribbon	4.33" x 298', 0.5" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes
HT-TT822OUT	Clean Start® Thermal Transfer Ribbon	4.33" x 984', 1.0" Core	PET, Black, 1/pkg	No	-	Yes
HT-TT100OUT	Clean Start® Thermal Transfer Ribbon	4.33" x 984', 1.0" Core	PET, Black, 1/pkg	No	+40°F to +300°F (+4°C to +82°C)	Yes